

SUBMITTAL: 1900 SERIES FIRE-FX2™ OLYMPUS™ SERIES AED & OXYGEN CABINET

PG 1 OF 2

Description: 1900 Series is designed to accommodate most AED's on the market today with room for an oxygen tank. Recessed models are ADAC-Compliant. Select from steel, stainless steel or aluminum construction.

Trim Construction: CRS with white powder-coat finish, #4 brushed stainless steel or clear anodized aluminum. 1-3/4" trim on face.

Door: Formed door with 1-3/4" trim, mounted in a 5/8" door stop with zinc-plated handle and roller catch and continuous hinge. All models feature a clear acrylic window with graphics enclosed, zinc-plated handle and roller catch.

Trim Style & Depth: *Recessed* – 3/8" flat trim, *Semi-Recessed* – 1 1/2" square edge or 3" or 2 1/2" rolled edge.

Alarm: 85 db Commander (audible) alarm standard.

Tub: The tub is constructed of cold rolled steel with white powder-coat finish standard. Fire-resistant material is attached to the exterior of the tub.

Please note that dimensions for wall opening have changed. See Chart on Page 2.

Oxygen: Accommodates up to "D" size cylinder. See options below.



Fire-Rating: Fire-FX2™ cabinets are fabricated in accordance with the UL label for one and two hour combustibile and non-combustibile wall system building codes. The fire testing has met the requirement of ANSI/UL 1479 (ASTM –E814) and ULC/CAN S115 for membrane and penetration firestops. Installation instructions must be strictly adhered to in order to obtain the fire rating.

STEP 1: SELECT MODEL NUMBER AND QUANTITY ON CHART (refer to chart on page 2)

A. Determine Trim Style according to wall depth.

B. Determine Tub I.D. according to size most suited for extinguisher and wall opening.



1915F12FX2
Cabinet with
3/8" Flat Trim
and Optional
Oxygen System

STEP 2: SELECT DOOR STYLE Check one box below

F12 Full Acrylic Glazing; Pull & AED Graphics

F17 Full Tempered Glazing; Pull & AED Decal

G12 Full Glazing; Acrylic, SAF-T-LOK™, Pull & AED Graphics

G17 Full Glazing; Tempered, SAF-T-LOK™, Pull & AED Decal

Horizontal Duo Panel; Acrylic, Pull & AED Decal

D17 Horizontal Duo Panel; Tempered, Pull & AED Decal

E12 Horizontal Duo Panel; Acrylic, SAF-T-LOK™, Pull & AED Decal

E17 Horizontal Duo Panel; Tempered, SAF-T-LOK™, Pull & AED Decal

S21 Solid Door; Pull & AED Decal

L22 Solid; SAF-T-LOK™, Pull & AED Decal

V12 Vertical Duo; Acrylic Glazing, Pull & AED Decal **D12**

V17 Vertical Duo; Tempered Glass, Pull & AED Decal

W12 Vertical Duo; Acrylic, SAF-T-LOK™, Pull & AED Decal

W17 Vertical Duo; Tempered, SAF-T-LOK™, Pull & AED Decal

Optional Features at Additional Cost:

(SA) [Siren Strobe Alarm](#) and 85 db Alarm (3" Trim Models Only)

(STC) Saf-T-Clasp for Visual Notification When Door has been opened

[Custom Door Graphics](#) available—company logos, photos, etc. Contact C. S.

AED Wall Signs ___14S ___14TX ___14XS - [See Separate Submittal](#)

Optional Colors [View Optional Colors Online](#) Contact Customer Service

Optional Anodized Aluminum [Finishes View Finishes Online](#)

[Bronze or Brass Finish](#) Contact Customer Service

(Pulls painted to match finish of color anodized, brass or bronze cabinets)

Optional Stainless Steel Finishes [View Finishes Online](#)

[LIF-O-GEN® Oxygen System](#) that features easy-to-use automatic flow system. (

(14MAG) Magnetic Door Contact for Existing Alarm Systems

(14RR) Roller Reed Ball Contact for Existing Alarm Systems

Custom Colors (Provide Paint Chip) Contact Customer Service

Optional Tub Color: ___Black ___Red

Etched or Engraved Lettering in Glass or Metal [More Info.](#)

[Recessed Pull, Pulls in Other Finishes, Lever Handle](#)


 <p>ACTIVAR INC. Construction Products Group www.activargroup.com</p> <p>1900 FX AND SAF-T-LOK ARE TRADEMARKS OF ACTIVAR PLEASE DOWNLOAD MOST CURRENT SUBMITTAL FROM WEBSITE BEFORE ORDERING</p>	Distributor:	Quantity:	
	Contractor:	Approved By:	
	Model #:	Architect:	
	Project:	Date:	© Activar Construction Products Group, Inc 2015
			10/5/2015



FOR MORE INFORMATION CALL 1-888-926-1365

Superior Specialty Supply • 9 Council Drive • PO Box 417 • Woodsboro, MD 21798 • www.sssupply.com


SUBMITTAL: 1900 FIRE-FX2™ OLYMPUS™ SERIES AED & OXYGEN CABINET



**FX2 Wall Opening
New Dimensions in 2015 - Please
Note**




New Lighter, FX2 Insulation



**3/8" (.9cm)
FLAT TRIM**

**1-1/2" (3.8cm)
SQUARE TRIM**

**2-1/2" (6.4cm)
ROLLED EDGE**



TRIM & DOOR MATERIAL & SERIES #							TUB I.D.			FRAME O.D.		FX Wall Opening New Dimensions 2015 - Please Note		
QTY	STEEL	QTY	ALUMINUM	QTY	STAINLESS STEEL	TRIM STYLE	A	B	C	E	F	W	H	D
	1915FX2		1925FX2		1935FX2	3/8" Flat Trim	18"	18"	8"	21-3/8"	21-3/8"	20 5/16"	20 5/16"	8-15/16"
	1916FX2		1926FX2		1936FX2	1-1/2" Square	18"	18"	8"	21-3/8"	21-3/8"	20 5/16"	20 5/16"	7-11/16"
	1917FX2		*1927FX2		1937FX2	3" Rolled or 2-1/2"	18"	18"	8"	21-3/8"	21-3/8"	20 5/16"	20 5/16"	*6-3/16"

* Model 1927 has 2-1/2" Trim & Requires 5/8" Deeper Wall Opening



FOR MORE INFORMATION CALL 1-888-926-1365

Superior Specialty Supply • 9 Council Drive • PO Box 417 • Woodsboro, MD 21798 • www.sssupply.com